### §84.178

(3) Designed and constructed to prevent inward leakage of contaminated air

### §84.178 Head harnesses; minimum requirements.

- (a) All facepieces shall be equipped with head harnesses designed and constructed to provide adequate tension during use and an even distribution of pressure over the entire area in contact with the face.
- (b) Facepiece head harnesses, except those employed on single-use respirators, shall be adjustable and replaceable.
- (c) Mouthpieces shall be equipped, where applicable, with adjustable and replaceable harnesses, designed and constructed to hold the mouthpiece in place.

## § 84.179 Non-powered air-purifying particulate respirators; filter identification.

- (a) The respirator manufacturer, as part of the application for certification, shall specify the filter series and the filter efficiency level (i.e., "N95", "R95", "P95", "N99, "R99", "P99", "N100", "R100", or "P100") for which certification is being sought.
- (b) Filters shall be prominently labeled as follows:
- (1) N100 filters shall be labeled "N100 Particulate Filter (99.97% filter efficiency level)" and shall be a color other than magenta.
- (2) R100 filters shall be labeled "R100 Particulate Filter (99.97% filter efficiency level)" and shall be a color other than magenta.
- (3) P100 filters shall be labeled "P100 Particulate Filter (99.97% filter efficiency level)" and shall be color coded magenta.
- (4) N99 filters shall be labeled "N99 Particulate Filter (99% filter efficiency level)" and shall be a color other than magenta.
- (5) R99 filters shall be labeled "R99 Particulate Filter (99% filter efficiency level)" and shall be a color other than magenta.
- (6) P99 filters shall be labeled "P99 Particulate Filter (99% filter efficiency level)" and shall be a color other than magenta.

- (7) N95 filters shall be labeled as "N95 Particulate Filter (95% filter efficiency level)" and shall be a color other than magenta.
- (8) R95 filters shall be labeled as "R95 Particulate Filter (95% filter efficiency level)" and shall be a color other than magenta.
- (9) P95 filters shall be labeled as "P95 Particulate Filter (95% filter efficiency level)" and shall be a color other than magenta.

#### §84.180 Airflow resistance tests.

- (a) Resistance to airflow will be measured in the facepiece, mouthpiece, hood, or helmet of a particulate respirator (complete respirator) mounted on a test fixture with air flowing at continuous rate of 85 ±2 liters per minute, before each test conducted in accordance with §84.182.
- (b) The resistances for particulate respirators upon initial inhalation shall not exceed 35 mm water column height pressure and upon initial exhalation shall not exceed 25 mm water column height pressure.

# § 84.181 Non-powered air-purifying particulate filter efficiency level determination.

- (a) Twenty filters of each non-powered air-purifying particulate respirator model shall be tested for filter efficiency against:
- (1) A solid sodium chloride particulate aerosol as per this section, if N-series certification is requested by the applicant.
- (2) A dioctyl phthalate or equivalent liquid particulate aerosol as per this section, if R-series or P-series certification is requested by the applicant.
- (b) Filters including holders and gaskets; when separable, shall be tested for filter efficiency level, as mounted on a test fixture in the manner as used on the respirator.
- (c) Prior to filter efficiency testing of 20 N-series filters, the 20 to be tested shall be taken out of their packaging and placed in an environment of 85  $\pm 5$  percent relative humidity at 38  $\pm 2.5~^{\circ}\mathrm{C}$  for 25  $\pm 1$  hours. Following the pre-conditioning, filters shall be sealed in a gas-tight container and tested within 10 hours.

#### Public Health Service, HHS

- (d) When the filters do not have separable holders and gaskets, the exhalation valves shall be blocked so as to ensure that leakage, if present, is not included in the filter efficiency level evaluation.
- (e) For non-powered air-purifying particulate respirators with a single filter, filters shall be tested at a continuous airflow rate of 85 ±4 liters per minute. Where filters are to be used in pairs, the test-aerosol airflow rate shall be 42.5 ±2 liters per minute through each filter.
- (f) Filter efficiency test aerosols. (1) When testing N-series filters, a sodium chloride or equivalent solid aerosol at  $25 \pm 5$  °C and relative humidity of  $30 \pm 10$  percent that has been neutralized to the Boltzmann equilibrium state shall be used. Each filter shall be challenged with a concentration not exceeding 200 mg/m<sup>3</sup>
- (2) When testing R-series and P-series filters, a neat cold-nebulized dioctyl phthalate (DOP) or equivalent aerosol at  $25 \pm 5$  °C that has been neutralized to the Boltzmann equilibrium state shall be used. Each filter shall be challenged with a concentration not exceeding 200 mg/m<sup>3</sup>.
- (3) The test shall continue until minimum efficiency is achieved or until an aerosol mass of at least 200  $\pm 5$  mg has contacted the filter. For P-series filters, if the filter efficiency is decreasing when the 200  $\pm 5$  mg challenge point is reached, the test shall be continued until there is no further decrease in efficiency.
- (g) The sodium chloride test aerosol shall have a particle size distribution with count median diameter of 0.075  $\pm 0.020$  micrometer and a standard geometric deviation not exceeding 1.86 at the specified test conditions as determined with a scanning mobility particle sizer or equivalent. The DOP aerosol shall have a particle size distribution with count median diameter of 0.185  $\pm 0.020$  micrometer and a standard geometric deviation not exceeding 1.60 at the specified test conditions as determined with a scanning mobility particle sizer or equivalent.
- (h) The efficiency of the filter shall be monitored and recorded throughout the test period by a suitable forward-

light-scattering photometer or equivalent instrumentation.

(i) The minimum efficiency for each of the 20 filters shall be determined and recorded and be equal to or greater than the filter efficiency criterion listed for each level as follows:

P100, R100 and N100: Efficiency ≥99.97% P99, R99 and N99: Efficiency ≥99% P95, R95 and N95: Efficiency ≥95%

### §84.182 Exhalation valve leakage test; minimum requirements.

- (a) Dry exhalation valves and valve seats will be subjected to a suction of 25 mm. water-column height while in a normal operating position.
- (b) Leakage between the valve and valve seat shall not exceed 30 milliliters per minute.

## Subpart L—Chemical Cartridge Respirators

### §84.190 Chemical cartridge respirators: description.

(a) Chemical cartridge respirators including all completely assembled respirators which are designed for use as respiratory protection during entry into or escape from atmospheres not immediately dangerous to life and health, are described according to the specific gases or vapors against which they are designed to provide respiratory protection, as follows:

Type of chemical cartridge respirator <sup>1</sup>	Maximum use con- centration, parts per million
Ammonia	300
Chlorine	10
Hydrogen chloride	50
Methyl amine	100
Organic vapor	21,000
Sulfur dioxide	50
Vinyl chloride	10

<sup>1</sup>Not for use against gases or vapors with poor warning properties (except where MSHA or Occupational Safety and Health Administration standards may permit such use for a specific gas or vapor) or those which generate high heats of reaction with sorbent material in the cartridge.

<sup>2</sup>Maximum use concentrations are lower for organic vapors which preduces atmembers immediately hazardays to life or

which produce atmospheres immediately hazardous to life or health at concentrations equal to or lower than this concentration.

(b) Chemical cartridge respirators for respiratory protection against gases or vapors, which are not specifically listed with their maximum use concentration, may be approved if the applicant